

®  
*TDS 0037*  
*Established: 23 Apr 2010*  
*Updated: 14 Nov 2017*

**TECHNICAL DATA SHEET FOR**

**BIODUR UNIVERSAL SPRAY PAINT**

|                    |   |
|--------------------|---|
| <b>DESCRIPTION</b> | Alkyd-based aerosol paint that is specially formulated for decorative and protective purposes.<br>It is suitable for both interior and exterior surfaces  |
| <b>TYPE</b>        | Alkyd-based   |
| <b>COLOUR</b>      | 36 RAL colors + church gold, copper, bronze   |
| <b>USES</b>        | Fast-drying enamel for painting metallic, concrete, gypsum, wooden, glass and other surfaces.<br>Convenient for working with stencils. Forms a durable glossy coating, resistant to mechanical and weathering impacts. Does not fade out in the sun and does not lose its gloss.  |
| <b>FEATURES</b>    | <ul style="list-style-type: none"><li>• Multipurpose, quick dry spray paint</li><li>• Extremely fast curing</li><li>• Good adhesion on various surfaces</li><li>• High gloss effect</li><li>• Good film properties such as hardness and flexibility</li><li>• Easy application</li><li>• Excellent colour uniformity (in RAL)</li></ul> |

|                             |  |
|-----------------------------|--|
| <b>APPLICATION DATA</b>     |  |
| <b>METHOD</b>               | Spray  |
| <b>THEORETICAL COVERAGE</b> | Depending on coat thickness and color is 1.5–2.0 m <sup>2</sup> .  |
| <b>INSTRUCTIONS:</b>        | <ol style="list-style-type: none"><li>1. Prepare surface: clean, polish, degrease.</li><li>2. Shake can for 2–3 min. Shake from time to time when using.</li><li>3. Spray to test.</li><li>4. Hold can upright. Apply enamel at 25–30 cm distance. Apply 2–3 thin coats at 3–5 min. intervals.</li><li>5. Attention! If enamel has not been used up, turn can injector downwards and spray till flow gets transparent.</li></ol> |
| <b>DRYING TIME</b>          | Drying time 7–10 min. at t +25°C.  |
| <b>INGREDIENTS:</b>         | Alkyd enamel, organic solvents mixture, propane, butane.   |